PCN Nu	mber:		201	5092900	)31	В			PCI	N Dat	e:	01/18/2016
Title: Assembly site move from Amkor K1 to Amkor P1 for Select Devices												
Custom	Customer Contact: PCN Manager Dept: Quality Services								ality Services			
Propose	ed 1 <sup>st</sup> Shi	p Da	te:	04/18/	20	)16	Estimated Sample Availability:	•	Date provided at sample request			
Change	Туре:						-					
Asse	embly Site	9				Desig	gn		W	/afer l	Bum	p Site
	embly Pro	cess				Data	Sheet					p Material
	embly Mat				Щ		number change	ĻĻ	-			p Process
_	hanical Sp					Test		Ļ		/afer		
	king/Shipp	oing/i	<u> abeli</u>	ng		Test	Process	┝				Materials
						D	CN Details		J VV	<i>l</i> aler l	гар і	Process
Descrint	tion of Ch	hang	e:			<u> </u>	CN Details					
Descript		idiig	<u> </u>									
notification Affected notice for Assembly	Revision B is to announce the <u>addition</u> of new devices that were not included on the original PCN notification. These new devices are bolded and highlighted in the device list below under Product Affected Group 2. The expected first shipment date for these new devices will be 90 days from this notice for these newly added devices only.  Assembly site move from Amkor K1 to Amkor P1 for Select Devices listed in the "Product Affected" Section. Material differences are as follows:											
Assemb	ly Site A	Assem	embly Site Origin			Site	City					
Amko			AMN			KR			Seoul			
Amko	r P1		AKI	₹			PH	Cupang, Muntinlupa City		ıpa City		
	Differen		ľ									
				Amko	r I	<b>K1</b>	Amkor P1					
Mount (	Compound	d		10133	39127 1013		101380679	80679				
Mold Co	mpound			10136	05	71	101385017					
Group 2 Devices:												
No material differences between sites.												
Reason for Change:												
Closure of the Amkor K1 assembly facility. Continuity of supply.												
Anticipa	ted impa	act o	n For	m, Fit,	Fι	ınctio	n, Quality or Relia	bili	ty (¡	positi	ive /	negative):
None.												
Changes	s to prod	uct i	denti	fication	ı r	esulti	ing from this PCN:					

## **Sample Product Shipping Label** (not actual product label)

Group 1: Assembly Site

Amkor K1	Assembly Site Origin (22L)	ASO: AMN
Amkor P1	Assembly Site Origin (22L)	ASO: AKR



ITEM: LBL: 5A (L)TO:375



(1P) \$N74L\$07N\$R (Q) 2000 (D) 0336 (31T)LOT: 3959047MLA (4W) TKY(1T) 7523483812

(2P) REV: (V) 0033317 (<del>20L) CSO: SHE</del> (21L) CCO:USA (22L) ASO: MLA (23L) ACO: MYS

ASSEMBLY SITE CODES: AMN =7, AKR = 4

### **Product Affected Group 1:**

AFE9006RFD

## **Product Affected Group 2:**

74SSTVF16859G4RG4	ADS1258IRTCT	DDC118IRTCR	MM9635-LQ3/NOPB
ADS1158IRTCR	BQ29312ARTHR	DDC118IRTCT	SN74SSTV16859RGQ8
ADS1158IRTCT	DDC114IRTCR	HPA00025S8	SN74SSTV16859RGQR
ADS1258IRTCR	DDC114IRTCT	MM9603-LQ4/NOPB	74SSTV16859RGQ8G3
ADS1158IRTCTG4	BQ29312ARTHRG4	HPA00022RGQ8	SN74SSTVF16859S8
ADS1258IRTCRG4	DDC114IRTCTG3	HPA00022RGQR	SN74SSTVF16859S8G3
ADS1258IRTCTG4	DDC118IRTCTG4	SN74SSTVF16859G4R	

# Group 1: Qualification Report Amkor K1 to P1 transfer of AFE9006RFD

#### **Product Attributes**

Attributes	Qual Device: AFE9006RFD
Assembly Site	AP1
Package Family	HTFQP
Wafer Fab Supplier	DMOS5
Wafer Process	1833 CO5

<sup>-</sup> QBS: Qual By Similarity

### **Qualification Results**

Data Displayed as: Number of lots / Total sample size / Total failed

Туре	Test Name / Condition	Duration	Qual Device: AFE9006RFD
AC	Autoclave 121C	96 Hours	3/231/0
HAST	Biased HAST, 130C/85%RH	96 Hours	3/231/0
HTSL	High Temp. Storage Bake, 170C	420 Hours	3/231/0

<sup>-</sup> Qual Device AFE9006RFD is qualified at LEVEL3-260C

LI	Lead Fatigue	Leads	3/66/0
LI	Lead Pull to Destruction	Leads	3/66/0
PD	Physical Dimensions		3/30/0
TC	Temperature Cycle, -65/150C	500 Cycles	3/231/0
WBP	Bond Pull	Wires	3/90/0
WBS	Ball Bond Shear	Wires	3/90/0

- Preconditioning was performed for Autoclave, Unbiased HAST, THB/Biased HAST, Temperature Cycle, Thermal Shock, and HTSL, as applicable
- The following are equivalent HTOL options based on an activation energy of 0.7eV: 125C/1k Hours, 140C/480 Hours, 150C/300 Hours, and 155C/240 Hours
- The following are equivalent HTSL options based on an activation energy of 0.7eV: 150C/1k Hours, and 170C/420 Hours
- The following are equivalent Temp Cycle options per JESD47 : -55C/125C/700 Cycles and -65C/150C/500 Cycles Quality and Environmental data is available at Tl's external Web site: http://www.ti.com/

#### **Green/Pb-free Status:**

Qualified Pb-Free(SMT) and Green

# Group 2: Qualification Report QFN transfer from Amkor K1 to Amkor P1

## **Product Attributes**

Attributes	Qual Device: ADS1158IRTC	Qual Device: DDC118IRTCR	Qual Device: MM9603-LQ4/NOPB	Qual Device: ADC12J4000NKER / LM15851
Assembly Site	AP1	AP1	AP1	AP1
Package Family	QFN	QFN	QFN	QFN
Wafer Fab Supplier	DMOS 5	TSMC-WF2	MAINEFAB	UMC12A
Wafer Process	50HPA07	0.50UM-TSMC	C80L18M2	UMC65NM

- QBS: Qual By Similarity
- Qual Device ADC12J4000NKER / LM15851 is qualified at LEVEL3-260C
- Qual Device ADS1158IRTC is qualified at LEVEL2-260C
- Qual Device DDC118IRTCR is qualified at LEVEL3-260C
- Qual Device MM9603-LQ4/NOPB is qualified at LEVEL4-260C
- Device DDC118IRTCR contains multiple dies.

#### **Qualification Results**

Data Displayed as: Number of lots / Total sample size / Total failed

Туре	Test Name / Condition	Duration	Qual Device: ADS1158IRTC	Qual Device: DDC118IRTCR	Qual Device: MM9603- LQ4/NOPB	Qual Device: ADC12J4000 NKER / LM15851
AC	Autoclave 121C	96 Hours	1/77/0	3/231/0	1/77/0	-
DS	Die Shear	-	1/10/0	3/90/0	1/10/0	-
HAST	Biased HAST, 130C/85%RH	96 Hours	-	3/231/0	-	-
HTSL	High Temp. Storage Bake, 170C	420 Hours	-	3/231/0	-	3/231/0
PD	Physical Dimensions	(per mechanical drawing)	1/5/0	3/15/0	1/5/0	3/15/0

Туре	Test Name / Condition	Duration	Qual Device: ADS1158IRTC	Qual Device: DDC118IRTCR	Qual Device: MM9603- LQ4/NOPB	Qual Device: ADC12J4000 NKER / LM15851
TC	Temperature Cycle, - 65/150C	500 Cycles	1/77/0	3/228/0	1/77/0	3/231/0
WBP	Bond Pull	Wires	1/30/0	3/90/0	1/30/0	3/90/0
WBS	Ball Bond Shear	Bonds	1/30/0	3/90/0	1/30/0	3/90/0
XRAY	X-ray	(top side only)	1/5/0	3/15/0	1/5/0	3/15/0

<sup>-</sup> Preconditioning was performed for Autoclave, Unbiased HAST, THB/Biased HAST, Temperature Cycle, Thermal Shock, and HTSL, as applicable

- The following are equivalent HTOL options based on an activation energy of 0.7eV : 125C/1k Hours, 140C/480 Hours, 150C/300 Hours, and 155C/240 Hours
- The following are equivalent HTSL options based on an activation energy of 0.7eV: 150C/1k Hours, and 170C/420 Hours
- The following are equivalent Temp Cycle options per JESD47 : -55C/125C/700 Cycles and -65C/150C/500 Cycles Quality and Environmental data is available at Tl's external Web site: http://www.ti.com/

#### Green/Pb-free Status:

Qualified Pb-Free(SMT) and Green

For questions regarding this notice, e-mails can be sent to the regional contacts shown below or your local Field Sales Representative.

Location	E-Mail
USA	PCNAmericasContact@list.ti.com
Europe	PCNEuropeContact@list.ti.com
Asia Pacific	PCNAsiaContact@list.ti.com
Japan	PCNJapanContact@list.ti.com